



No.	ITEM#	DESCRIPTION	QTY.	NOTES
1	JZSP-CMM9-1	CONNECTOR CAP, MFG#: 350780-1	1	AMP
2		SOCKET (PIN 1~4), MFG#: 350570-3 or 350689-3	4	AMP
3	<del>JM54457</del> JM54458	CABLE, FLEXIBLE PVC, 20AWG x 4C,BLACK,SHIELDED	-	James Monroe Wire&Cable
4	1.25-M4 or 1.25-4M	RING TERMINAL	1	JST or Nichifu
5	216-102	UNINSULATED FERRULE (L=8mm)	3	Wago
6	UNP00058-1	CAUTION TAG	1	ULINE



CABLE SPECIFICATION (mm)	
OUTER DIAMETER	9.14
BENDING RADIUS	10 O.D.
STANDARD	UL/CE
UL/IP CLASSIFICATION	
CONNECTOR SPEC	UL94V-0



ITEM NUMBER	X=LENGTH(mm)
BAHCE-03(A)	3000
BAHCE-05(A)	5000
BAHCE-10(A)	10000
BAHCE-15(A)	15000
BAHCE-20(A)	20000

**NOTES:**

- ADD APPROPRIATE HEAT SHRINK TUBE.
- MARKER TUBE
- YASKAWA INFORMATION LABEL : 

**YASKAWA**  
**"ITEM NUMBER" ("REV")**  
**"VENDOR CODE" "MM/YY"**
- MARKER FLAG
- REFER TO DRAWING UNP00058 FOR CAUTION TAG INFORMATION

	CHANGE RAW CABLE	6-30-05	JAKUBOWSKI	N-0506-006
	REDRAW;CHANGE RAW CABLE	4-18-05	JAKUBOWSKI	N-0504-002

DESIGN: -	-	MATERIAL: SEE PART LIST ABOVE
DRWN: J. ALFONSO	10-5-98	SPEC: SEE PART LIST ABOVE
CHKD: D. BRENDLEY	3-25-99	FINISH: N/A
TECH: D. BRENDLEY	4-13-99	TOLERANCES/REFERENCES: UES000002
APRV: M. MORAN	4-14-99	
THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA ELECTRIC AMERICA INC.		MODEL(S): SGMAH & SGMPH
		REF DWG: JZSPCM00-X (A)
DIMENSIONS: mm		SCALE: NTS
SIZE: B		SHEET: 1/1

**YASKAWA**  
Energy In Motion™

TITLE: **CE SERVO MOTOR CABLE NO BRAKE, SGMAH & SGMPH**

DWG: **UWR00314**

ITEM #: **\*SEE CHART**