



V74X NEMA 4X

RATED INPUT	MODEL # CIMR-V7xx	AMPS	HP	WT LBS
230V	25P54	25	7.5	41.5
	27P54	33	10	41.5
460V	45P54	14.8	7.5 & 10	41.5
	47P54	21	15	41.5

xx denotes AA-ZZ

UNITS: <sup>inch</sup>  
[mm]

FOR REFERENCE ONLY UNLESS PROPERLY ENDORSED.



DR BY RIP 7.9.02  
APPVL SR 7.9.02  
REV. JCM 9.16.02