

A.C. INPUT

Volts: _____ Hz: _____
Phase: _____ Amps: _____

SCCR: _____

A.C. OUTPUT

Volts: _____ Hz: _____
Phase: _____ Amps: _____

Designator	Rating	Type
F1, F2		
F6		
F7		
F3, F4, F5		
F8, F9, F10		

Serial No.: _____
Model No.: _____
Type.: _____
W.D.: _____
Inst. Manual.: _____

YASKAWA

SUMMARY OF PAGES		
PRODUCT	SCCR	INFO
A1C1	PAGES 2 AND 3	
A1C2	PAGES 4 AND 5	
A1C3	PAGES 10 AND 11	
A1C4	PAGES 6 AND 7	
A1C5	PAGES 8 AND 9	
A1C6	PAGES 12 AND 13	

FIGURE 1

SCCR: ① kA rms sym., ② V max.

USE FORMAT: UNPN0078-SCCR 1

SCCR: ① kA rms sym., ② V max.,
with ③ A max., Class ④ fuses

USE FORMAT: UNPN0078-SCCR 2

SCCR: ① kA rms sym., ② V max.,
with ③ NTD fuses

USE FORMAT: UNPN0078-SCCR 3

SCCR: ① kA rms sym., ② V max.,
or
③ kA rms sym., ② V max.,
with ④ A max., Class ⑤ fuses

USE FORMAT: UNPN0078-SCCR 4

SCCR: ① kA rms sym., ② V max.,
with ③ kAIR min., ④ A fuses or MCCB

USE FORMAT: UNPN0078-SCCR 5

SCCR: ① kA rms sym., ② V max.,
with Class J/RK1 fuses
as per the
Drive Technical Manual

USE FORMAT: UNPN0078-SCCR 6

SCCR: ① kA rms sym., ② V max.,
with Branch Circuit Protection
as per the
Drive Technical Manual

USE FORMAT: UNPN0078-SCCR 7

YASKAWA

THIS DOCUMENT AND INFORMATION
CONTAINED IN IT ARE CONFIDENTIAL,
AND CANNOT BE COPIED OR
DISCLOSED IN WHOLE OR IN PART
WITHOUT THE EXPRESS WRITTEN
CONSENT OF YASKAWA AMERICA INC.

DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
CHECKED: D.R. CMELAK	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 1 of 13
TECH:	DATE:	DRAWING #: UDA00693		
APPROVED: K. FLIERL	DATE: 8/23/12			
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11			

REVISIONS				
REV.	DESCRIPTION	ECO #	DRAWN BY	DATE
07	CHANGED TABLE FORMATS FOR AUTO DATA LABEL CREATION	7218	DJP	06/27/16
06	CORRECTED W.O. PART NO. AND UPDATED YASKAWA LOGO	7213	KM	06/22/16
05	CHANGED SCCR DATA AND TABLE NUMBERS	5554	DRC	08/20/14

TABLE 1

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD				
	WITHOUT OPTIONS PF			WITH OPTIONS PF				①	②	①	②	USE FORMAT UNPN0078-SCCR_	①	②	③	④
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②										
A1C1A002	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A003	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A004	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A006	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A009	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A015	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A022	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A028	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A042	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---
A1C1A054	7	10	240	1	10	240	1	65	240	25	240	6	10	240	---	---
A1C1A068	7	10	240	1	10	240	1	65	240	25	240	6	10	240	---	---
A1C1A080	7	10	240	1	10	240	1	65	240	25	240	6	10	240	---	---
A1C1A104	7	10	240	1	10	240	1	65	240	25	240	5	65	240	65	150
A1C1A130	7	10	240	1	10	240	1	65	240	25	240	5	65	240	65	175
A1C1A154	7	10	240	1	10	240	1	65	240	25	240	5	65	240	65	250
A1C1A192	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	250
A1C1A248	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400
A1C1A312	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400
A1C1A360	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	600
A1C1B001	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B002	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B003	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B004	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B007	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B011	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B014	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B021	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B027	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B034	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B040	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B052	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---
A1C1B065	7	10	480	1	10	480	1	65	480	18	480	6	10	480	---	---
A1C1B077	7	10	480	1	10	480	1	65	480	18	480	6	10	480	---	---
A1C1B096	7	10	480	1	10	480	1	65	480	18	480	6	10	480	---	---
A1C1B124	7	10	480	1	10	480	1	65	480	18	480	5	65	480	65	150
A1C1B156	7	10	480	1	10	480	1	65	480	18	480	5	65	480	65	250
A1C1B180	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	250
A1C1B240	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400
A1C1B302	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400
A1C1B361	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400
A1C1B414	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	600
A1C1B477	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600
A1C1B515	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600
A1C1B590	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800
A1C1B660	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800
A1C1B720	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200
A1C1B810	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200
A1C1B900	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200
A1C1B930	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200
A1C1BK09	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1600
A1C1BK20	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 2 of 13
	ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693		

TABLE 2

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C1C1P3	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C1P7	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C002	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C003	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C006	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C009	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C011	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C017	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C022	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C027	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C032	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C041	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C1C052	7	10	600	1	10	600	1	50	600	14	600	6	10	600	---	---	6	10	600	---	---
A1C1C062	7	10	600	1	10	600	1	50	600	14	600	6	10	600	---	---	6	10	600	---	---
A1C1C077	7	10	600	1	10	600	1	50	600	14	600	6	10	600	---	---	6	10	600	---	---
A1C1C099	7	10	600	1	10	600	1	50	600	14	600	5	50	600	50	150	5	50	600	50	150
A1C1C125	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C1C144	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C1C192	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C1C242	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C1D002	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D003	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D004	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D006	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D007	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D010	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D016	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D024	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D030	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C1D046	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C1D059	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C1D074	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C1D088	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C1D114	7	10	208	1	10	208	1	65	208	25	208	5	65	208	65	150	5	65	208	65	150
A1C1D143	7	10	208	1	10	208	1	65	208	25	208	5	65	208	65	175	5	65	208	65	175
A1C1D169	7	10	208	1	10	208	1	65	208	25	208	5	65	208	65	250	5	65	208	65	250
A1C1D211	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	250	5	65	208	65	250
A1C1D273	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C1D343	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600
A1C1D396	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 3 of 13
	ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693		

TABLE 3

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF		WITH OPTION PF					①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C2A002	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A003	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A004	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A006	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A009	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A015	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A022	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A028	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A042	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A054	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A068	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A080	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A104	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A130	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A154	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C2A192	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	250	5	65	240	65	250
A1C2A248	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C2A312	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C2A360	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	600	5	65	240	65	600
A1C2B001	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B002	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B003	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B004	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B007	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B011	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B014	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B021	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B027	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B034	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B040	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B052	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B065	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B077	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B096	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B124	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B156	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C2B180	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	250	5	35	480	35	250
A1C2B240	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C2B302	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C2B361	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C2B414	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	600	5	35	480	35	600
A1C2B477	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C2B515	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C2B590	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C2B660	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C2B720	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C2B810	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C2B900	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C2B930	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C2BK09	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C2BK20	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1600	5	65	480	65	1600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 4 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 4

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C2C1P3	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C1P7	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C002	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C003	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C006	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C009	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C011	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C017	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C022	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C027	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C032	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C041	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C052	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C062	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C077	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C099	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C125	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C144	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C2C192	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C2C242	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C2D002	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D003	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D004	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D006	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D007	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D010	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D016	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D024	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D030	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D046	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D059	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D074	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D088	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D114	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D143	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D169	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C2D211	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	250	5	65	208	65	250
A1C2D273	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C2D343	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600
A1C2D396	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 5 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 5

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C4A002	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A003	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A004	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A006	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A009	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A015	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A022	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A028	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A042	7	10	240	1	10	240	1	65	240	25	240	6	5	240	---	---	6	5	240	---	---
A1C4A054	7	10	240	1	10	240	1	65	240	25	240	6	10	240	---	---	6	10	240	---	---
A1C4A068	7	10	240	1	10	240	1	65	240	25	240	6	10	240	---	---	6	10	240	---	---
A1C4A080	7	10	240	1	10	240	1	65	240	25	240	6	10	240	---	---	6	10	240	---	---
A1C4A104	7	10	240	1	10	240	1	65	240	25	240	5	65	240	65	150	5	65	240	65	150
A1C4A130	7	10	240	1	10	240	1	65	240	25	240	5	65	240	65	150	5	65	240	65	150
A1C4A154	7	10	240	1	10	240	1	65	240	25	240	5	65	240	65	175	5	65	240	65	175
A1C4A192	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	250	5	65	240	65	250
A1C4A248	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C4A312	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C4A360	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C4B001	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B002	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B003	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B004	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B007	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B011	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B014	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B021	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B027	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B034	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B040	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B052	7	10	480	1	10	480	1	65	480	18	480	6	5	480	---	---	6	5	480	---	---
A1C4B065	7	10	480	1	10	480	1	65	480	18	480	6	10	480	---	---	6	10	480	---	---
A1C4B077	7	10	480	1	10	480	1	65	480	18	480	6	10	480	---	---	6	10	480	---	---
A1C4B096	7	10	480	1	10	480	1	65	480	18	480	6	10	480	---	---	6	10	480	---	---
A1C4B124	7	10	480	1	10	480	1	65	480	18	480	5	65	480	65	150	5	65	480	65	150
A1C4B156	7	10	480	1	10	480	1	65	480	18	480	5	65	480	65	175	5	65	480	65	175
A1C4B180	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C4B240	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C4B302	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C4B361	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C4B414	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	600	5	35	480	35	600
A1C4B477	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C4B515	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C4B590	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C4B660	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C4B720	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C4B810	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C4B900	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C4B930	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C4BK09	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 6 of 13
	ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693		

TABLE 6

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C4C1P3	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C1P7	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C002	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C003	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C006	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C009	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C011	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C017	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C022	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C027	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C032	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C041	7	10	600	1	10	600	1	50	600	14	600	6	5	600	---	---	6	5	600	---	---
A1C4C052	7	10	600	1	10	600	1	50	600	14	600	6	10	600	---	---	6	10	600	---	---
A1C4C062	7	10	600	1	10	600	1	50	600	14	600	6	10	600	---	---	6	10	600	---	---
A1C4C077	7	10	600	1	10	600	1	50	600	14	600	6	10	600	---	---	6	10	600	---	---
A1C4C099	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C4C125	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C4C144	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C4C192	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C4D002	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D003	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D004	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D006	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D007	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D010	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D016	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D024	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D030	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D046	7	10	208	1	10	208	1	65	208	25	208	6	5	208	---	---	6	5	208	---	---
A1C4D059	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C4D074	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C4D088	7	10	208	1	10	208	1	65	208	25	208	6	10	208	---	---	6	10	208	---	---
A1C4D114	7	10	208	1	10	208	1	65	208	25	208	5	65	208	65	150	5	65	208	65	150
A1C4D143	7	10	208	1	10	208	1	65	208	25	208	5	65	208	65	175	5	65	208	65	175
A1C4D169	7	10	208	1	10	208	1	65	208	25	208	5	65	208	65	250	5	65	208	65	250
A1C4D211	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	250	5	65	208	65	250
A1C4D273	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C4D343	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C4D396	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 7 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 7

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF		WITH OPTION PF		USE FORMAT UNPN0078-SCCR_	①		②	①	②	WITHOUT OPTION PF				WITH OPTION PF						
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_							①	②	USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③
A1C5A002	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A003	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A004	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A006	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A009	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A015	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A022	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A028	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A042	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A054	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A068	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A080	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A104	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A130	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A154	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C5A192	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	250	5	65	240	65	250
A1C5A248	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C5A312	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C5A360	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C5B001	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B002	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B003	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B004	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B007	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B011	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B014	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B021	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B027	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B034	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B040	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B052	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B065	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B077	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B096	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B124	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B156	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B180	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C5B240	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C5B302	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C5B361	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C5B414	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	600	5	35	480	35	600
A1C5B477	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C5B515	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C5B590	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C5B660	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C5B720	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C5B810	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C5B900	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C5B930	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C5BK09	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 8 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 8

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD,PE OR PJ						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTIONS PE OR PJ		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C5C1P3	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C1P7	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C002	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C003	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C006	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C009	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C011	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C017	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C022	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C027	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C032	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C041	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C052	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C062	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C077	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C099	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C125	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C144	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C5C192	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C5D002	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D003	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D004	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D006	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D007	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D010	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D016	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D024	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D030	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D046	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D059	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D074	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D088	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D114	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D143	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D169	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C5D211	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	250	5	65	208	65	250
A1C5D273	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C5D343	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C5D396	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 9 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 9

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD, OR PE						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTION PE		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C3A002	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A003	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A004	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A006	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A009	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A015	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A022	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A028	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A042	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A054	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A068	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A080	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A104	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A130	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A154	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C3A192	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	250	5	65	240	65	250
A1C3A248	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C3A312	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C3A360	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	600	5	65	240	65	600
A1C3B001	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B002	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B003	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B004	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B007	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B011	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B014	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B021	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B027	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B034	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B040	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B052	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B065	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B077	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B096	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B124	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B156	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C3B180	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	250	5	35	480	35	250
A1C3B240	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C3B302	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C3B361	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C3B414	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	600	5	35	480	35	600
A1C3B477	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C3B515	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C3B590	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C3B660	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C3B720	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C3B810	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C3B900	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C3B930	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C3BK09	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1600	5	65	480	65	1600
A1C3BK20	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1600	5	65	480	65	1600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	<p>DRAWN BY: K. MALUSIC</p>	<p>DATE: 8/23/12</p>	<p>TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000</p>			
	<p>CHECKED: D.R. CMELAK</p>	<p>DATE: 8/23/12</p>				
	<p>TECH:</p>	<p>DATE:</p>				
	<p>APPROVED: K. FLIERL</p>	<p>DATE: 8/23/12</p>	<p>SIZE: C</p>	<p>REVISION: 07</p>	<p>PAGE: 10 of 13</p>	
<p>ORIGINAL DESIGN: D.R. CMELAK</p>		<p>DATE: 5/16/11</p>	<p>DRAWING #: UDA00693</p>			

TABLE 10

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD, OR PE						USE FORMAT UNPN0078-SCCR_	WITH OPTION PC		WITH OPTION PE		WITH OPTION PD									
	WITHOUT OPTION PF			WITH OPTION PF				①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C3C1P3	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C1P7	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C002	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C003	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C006	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C009	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C011	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C017	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C022	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C027	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C032	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C041	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C052	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C062	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C077	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C099	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C125	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C144	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C3C192	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C3C242	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C3D002	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D003	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D004	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D006	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D007	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D010	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D016	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D024	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D030	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D046	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D059	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D074	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D088	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D114	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D143	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D169	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C3D211	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	250	5	65	208	65	250
A1C3D273	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C3D343	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600
A1C3D396	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600


 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 11 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 11

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD, OR PE						WITH OPTION PC		WITH OPTION PE		WITH OPTION PD										
	WITHOUT OPTION PF			WITH OPTION PF			USE FORMAT UNPN0078-SCCR_	①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C6A002	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A003	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A004	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A006	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A009	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A015	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A022	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A028	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A042	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A054	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A068	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A080	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A104	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A130	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A154	7	10	240	1	10	240	1	65	240	25	240	7	5	240	---	---	1	5	240	---	---
A1C6A192	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	250	5	65	240	65	250
A1C6A248	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C6A312	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C6A360	7	10	240	1	10	240	1	65	240	65	240	5	65	240	65	400	5	65	240	65	400
A1C6B001	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B002	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B003	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B004	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B007	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B011	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B014	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B021	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B027	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B034	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B040	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B052	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B065	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B077	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B096	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B124	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B156	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B180	7	10	480	1	10	480	1	65	480	18	480	7	5	480	---	---	1	5	480	---	---
A1C6B240	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C6B302	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C6B361	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	400	5	35	480	35	400
A1C6B414	7	10	480	1	10	480	1	65	480	35	480	5	35	480	35	600	5	35	480	35	600
A1C6B477	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C6B515	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	600	5	65	480	65	600
A1C6B590	7	10	480	1	10	480	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C6B660	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	800	5	65	480	65	800
A1C6B720	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C6B810	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C6B900	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C6B930	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200
A1C6BK09	1	10	480	---	---	---	1	65	480	35	480	5	65	480	65	1200	5	65	480	65	1200



 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 12 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			

TABLE 12

WORK ORDER PART NO. BEGINNING	WITHOUT OPTIONS PC,PD, OR PE						WITH OPTION PC		WITH OPTION PE		WITH OPTION PD										
	WITHOUT OPTION PF			WITH OPTION PF			USE FORMAT UNPN0078-SCCR_	①	②	①	②	WITHOUT OPTION PF				WITH OPTION PF					
	USE FORMAT UNPN0078-SCCR_	①	②	USE FORMAT UNPN0078-SCCR_	①	②						USE FORMAT UNPN0078-SCCR_	①	②	③	④	USE FORMAT UNPN0078-SCCR_	①	②	③	④
A1C6C1P3	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C1P7	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C002	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C003	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C006	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C009	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C011	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C017	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C022	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C027	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C032	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C041	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C052	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C062	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C077	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C099	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C125	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C144	7	10	600	1	10	600	1	50	600	14	600	7	5	600	---	---	1	5	600	---	---
A1C6C192	7	10	600	1	10	600	1	25	600	18	600	5	18	600	18	400	5	18	600	18	400
A1C6D002	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D003	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D004	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D006	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D007	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D010	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D016	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D024	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D030	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D046	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D059	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D074	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D088	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D114	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D143	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D169	7	10	208	1	10	208	1	65	208	25	208	7	5	208	---	---	1	5	208	---	---
A1C6D211	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	250	5	65	208	65	250
A1C6D273	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C6D343	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	400	5	65	208	65	400
A1C6D396	7	10	208	1	10	208	1	65	208	65	208	5	65	208	65	600	5	65	208	65	600

 <p>THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.</p>	DRAWN BY: K. MALUSIC	DATE: 8/23/12	TITLE: AC DRIVE DATA NAMEPLATE SHORT CIRCUIT RATING DATA FORMAT FOR A1000		
	CHECKED: D.R. CMELAK	DATE: 8/23/12			
	TECH:	DATE:			
	APPROVED: K. FLIERL	DATE: 8/23/12	SIZE: C	REVISION: 07	PAGE: 13 of 13
ORIGINAL DESIGN: D.R. CMELAK	DATE: 5/16/11	DRAWING #: UDA00693			