


# DriveWorksEZ<sup>®</sup> Software

## Programming for the V1000 and A1000 Series Drives



 **YASKAWA**<sup>™</sup>

# The Intelligent Choice for Distributed Control


## DriveWorksEZ® Programming Software

The marketplace is moving towards flexible drive software that allows the user to adapt their drive to machines/processes in a timely and cost effective manner. DriveWorksEZ® adds programmable drive functions that can tailor the V1000 and A1000 Series drives to the machine without the help of external controllers such as a PLC. This provides the user with easy access to the power of the V1000 and A1000 Series drives through an icon-based, graphical programming environment.

DriveWorksEZ® is a software system that provides the means to create custom drive functionality

inside the V1000 and A1000 Series drives. The system is composed of dedicated V1000 and A1000 Series drive software and a PC tool for creating and downloading function-block based application programs. Simply create application programs by arranging function block icons in a visual flow chart. Total drive and machine control are only a few mouse clicks away. User-friendly program monitoring is included for fast, easy start-up and troubleshooting.

DriveWorksEZ® provides function on demand, allowing the customer to customize and adapt the V1000 and A1000 Series drives to their machine needs in a fast and intuitive manner.



Example Application - Center Winder with Dancer Control and Diameter Calculation

## Open Architecture

DriveWorksEZ® offers a variety of communication options. This makes it an ideal choice for most machine designs. Network interface options including DeviceNet, Profibus-DP, EtherNet/IP, Modbus TCP/IP, MECHATROLINK-II, and others allow the V1000 and A1000 Series drives with DriveWorksEZ® to be a powerful node on the factory network. DriveWorksEZ® offers distributed, high-speed control that can off-load PLC processing and improve machine performance.

The V1000 and A1000 Series drives with DriveWorksEZ® can independently provide a complete machine solution for many applications, eliminating the need for PLCs or other controllers. This means reduced cost, design simplicity, and one-source responsibility.

## User Friendly Start-up and Programmability

### Easy to Use

DriveWorksEZ® has an intuitive, easy to use programming interface. Application programs can be created in a matter of minutes. Compiling and downloading take seconds resulting in less development time.

### Fast Execution Time

DriveWorksEZ® has a fast execution time, regardless of program size or complexity. This guarantees maximum performance for every application by allowing for more precise machine operation over a greater operating range.

### Flexible

DriveWorksEZ® has a wide variety of function blocks to choose from. All drive commands and monitors are available allowing for nearly unlimited control schemes. Machine design and control is more flexible than with a central controller.

### On-Line Monitoring

DriveWorksEZ® makes it easy to debug and troubleshoot an application program. The status of each function block is continuously updated which takes the guesswork out of troubleshooting the program.

### Process Control

DriveWorksEZ® includes a comprehensive PID control function block for machine processes. The PID control loop is extremely configurable and can be used to control almost any process variable.

### Sectional Machine Control

DriveWorksEZ® includes function blocks for diameter calculation and PID control. This is ideal for sectional drive systems requiring precise web control and winding through the use of dancers and load cells.

## DriveWorksEZ® Specifications

	V1000	A1000
<b>Programming</b>		
Number of available blocks	225	289
Number of block connections	50	100
Execution speed	2 mS	1 mS
Torque and speed loop update	2 mS	1mS
Function types	10 numeric, 10 logic	12 numeric, 12 logic
Drive data	All commands, monitors, and parameters	All commands, monitors, and parameters
<b>Standard I/O</b>		
Analog inputs	1 (0-10Vdc), 1 (0-10Vdc or 4-20mA / 0-20mA)	3 (0 +/- 10VDC, 4-20mA)
Analog outputs	1 (0-10Vdc)	2 (0 +/- 10VDC, 4-20mA)
Digital inputs	7	8
Digital outputs	1 (form C, 2 photo coupler)	3 (form A)
Fault contact	1 (Form C)	1 (form C)
Pulse train input	1 (32kHz)	1 (32kHz)
Pulse train output	1 (32kHz)	1 (32kHz)
RS-422/485	Modbus 115.2 kbps	Modbus 115.2 kbps
<b>Optional I/O</b>		
Analog inputs	x	3 (0 +/- 10VDC, 4-20mA)
Analog outputs	x	2 (0 +/- 10VDC)
Digital inputs	x	Binary (8, 12, or 16 Bit)
Digital outputs	x	8 (2 form A, 6 photo coupler)
Encoder inputs	x	2 (quadrature with compliments, 300kHz max)
<b>Network Communication</b>		
DeviceNet	o	o
Profibus-DP	o	o
EtherNet/IP	o	o
Modbus TCP/IP	o	o
MECHATROLINK-II	o	o

o - Available as option      x - Not available

### Available DriveWorksEZ® Function Block Types

- ▶ Drive and Option I/O
- ▶ Monitors
- ▶ Drive Commands
- ▶ Keypad Input/Output
- ▶ Digital/Numeric/Compound Functions
- ▶ Constants
- ▶ Communications
- ▶ Temporary Registers

### Global Certification

UL, cUL, CE, RoHS, and TUV

### Drive Ratings

Voltage	V1000	A1000
240 Vac	1/8 to 25 HP	3/4 to 150 HP
480 Vac	1/2 to 25 HP	3/4 to 1000 HP
600 Vac	N/A	1 to 100 HP



**Yaskawa America, Inc.**  
Drives & Motion Division

2121 Norman Drive South  
Waukegan, IL 60085  
Tel: 1-800-YASKAWA (927-5292) • Fax: 1-847-887-7310  
DrivesHelpDesk@yaskawa.com • [www.yaskawa.com](http://www.yaskawa.com)  
Document BL.DWEZ.01 12/1/2010 • © 2010