




The dimensions shown are for an IP20/Type 1 Drive that has been converted to a IP20/Backside Type 12 Drive by adding the parts from Type 12 heatsink external mounting kit number part number ZPSD-600-EH12-FR10

C/C: HV60□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
4302□□□	380 TO 480	126 (277)	2

□ denotes A-Z




EMC FILTER SWITCHES



C/C:	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
HV60□				
4302□□□	R/L1, S/L2, T/L3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
	U/T1, V/T2, W/T3	2/0 - 300 x 2P (70 - 150 x 2P)	M12	35 (310)
	-, +1	3 - 400 x 2P (35 - 240 x 2P)	M12	35 (310)
	⊕	1 - 350 (120 - 240)	M12	32 - 40 (283 - 354)

□ Denotes A-Z
 Note: Refer to applicable codes and standards for proper wire type and size.



8	YASKAWA		DRWN. J. MATTAS 2-20-20	TITLE HV600 DIMENSION DRAWING	SIZE A	PAGE 3 OF 3	REV
			CHKD. J. PIOTROWSKI 2-26-20	FRAME SIZE 10	DWG.NO.	0	
			TECH. L. UDDIN 3-9-20	BACKSIDE TYPE 12 ENCLOSURE	DD.HV60.FR10.FLNG		
			SCALE 1:8	APRV. J. CAIRO 3-12-20			