

C/C: GA80□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2257□□□	200 TO 240	69 (151.8)	2
2313□□□		69 (151.8)	2
4208□□□	380 TO 480	74 (162.8)	2
4250□□□		74 (162.8)	2
4302□□□		74 (162.8)	2

□ denotes A-Z

1	REVISED MOUNTING BKTS P2
0	INITIAL RELEASE




UNITS MM [IN]  
SCALE 1:10

DRWN.	J. MATTAS	4-9-19
CHKD.	J. PIOTROWSKI	5-6-19
TECH.	L. UDDIN	5-20-19
APRV.	J. CAIRO	6-13-19

TITLE  
GA800 DIMENSION DRAWING  
FRAME SIZE 9  
BACKSIDE TYPE 12 ENCLOSURE

SIZE	A	PAGE	1 OF 3
DWG.NO.	DD.GA80.FR9.FLNG		

REV  
1



C/C:	TERMINAL SYMBOL	WIRE RANGE AWG (mm <sup>2</sup> )	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
GA80□	R/L1, S/L2, T/L3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
2257□□□	U/T1, V/T2, W/T3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
4208□□□	-, +1, +3	2 - 250 x 2P (35 - 120 x 2P)	M10	20 (177)
4250□□□	⊕	2 - 350 (35 - 185)	M10	18 - 23 (159 - 204)
4302□□□				

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

8	
1	REVISED MOUNTING BKTS P2
0	INITIAL RELEASE



	UNITS MM [IN]
SCALE 1:8	


DRWN.	J. MATTAS	4-9-19
CHKD.	J. PIOTROWSKI	5-6-19
TECH.	L. UDDIN	5-20-19
APRV.	J. CAIRO	6-13-19

TITLE	GA800 DIMENSION DRAWING FRAME SIZE 9 BACKSIDE TYPE 12 ENCLOSURE
-------	---

SIZE	A	PAGE	2 OF 3
DWG.NO.	DD.GA80.FR9.FLNG		

REV	1
-----	---

Panel Cutout




Notes:

Exposed heatsink minimum clearance D = 165 [6.50].  
Refer to Type 12 heatsink external installation manual for additional details.

1	REVISED MOUNTING BKTS P2
0	INITIAL RELEASE

**YASKAWA**

  
 UNITS MM [IN]  
 SCALE 1:8

DRWN.	J. MATTAS	4-9-19
CHKD.	J. PIOTROWSKI	5-6-19
TECH.	L. UDDIN	5-20-19
APRV.	J. CAIRO	6-13-19

TITLE	GA800 DIMENSION DRAWING FRAME SIZE 9 BACKSIDE TYPE 12 ENCLOSURE
-------	---

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.GA80.FR9.FLNG		

REV 1