



C/C: GA80□	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2257□□□	200 TO 240	67 (147.4)	2
2313□□□		67 (147.4)	2
4208□□□		71 (156.2)	2
4250□□□	380 TO 480	71 (156.2)	2
4302□□□		71 (156.2)	2

□ denotes A-Z

YASKAWA		DRWN. J. MATTAS 6-27-18	TITLE GA800 DIMENSION DRAWING	SIZE A	PAGE 1 OF 3	REV 0
	UNITS MM [IN]	CHKD. J. PIOTROWSKI 7-9-18	FRAME SIZE 9	DWG.NO. DD.GA80.FR9.IP20		
	SCALE 1:10	TECH. L. UDDIN 7-16-18	IP20 ENCLOSURE			
		APRV. J. CAIRO 8-21-18				




C/C: GA80□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2257□□□	R/L1, S/L2, T/L3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
2313□□□	U/T1, V/T2, W/T3	3 - 4/0 x 2P (30 - 120 x 2P)	M10	20 (177)
4208□□□	-, +1, +3	2 - 250 x 2P (35 - 120 x 2P)	M10	20 (177)
4250□□□	⊕	2 - 350 (35 - 185)	M10	18 - 23 (159 - 204)
4302□□□				

□ Denotes A-Z

Note: Refer to applicable codes and standards for proper wire type and size.

YASKAWA



UNITS MM [IN]

SCALE 1:8


DRWN. J. MATTAS 6-27-18
 CHKD. J. PIOTROWSKI 7-9-18
 TECH. L. UDDIN 7-16-18
 APRV. J. CAIRO 8-21-18

TITLE
 GA800 DIMENSION DRAWING
 FRAME SIZE 9
 IP20 ENCLOSURE

SIZE A PAGE 2 OF 3
 DWG.NO. DD.GA80.FR9.IP20


REV
 0

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

Panel Cutout
For External Heatsink Mounting Configuration



Notes:
Exposed heatsink minimum clearance D = 165 [6.50].
Refer to external heatsink instructions document for additional details.

YASKAWA

UNITS MM [IN]
SCALE 1:8

DRWN.	J. MATTAS	6-27-18
CHKD.	J. PIOTROWSKI	7-9-18
TECH.	L. UDDIN	7-16-18
APRV.	J. CAIRO	8-21-18

TITLE	GA800 DIMENSION DRAWING FRAME SIZE 9 IP20 ENCLOSURE
-------	---

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.GA80.FR9.IP20		

REV
0