

C/C: HV600	INPUT VOLTAGE 3-PHASE (VAC)	WEIGHT Kg (lb)	COOLING FANS
2075	200 TO 240	25 (55.1)	2
2088		25 (55.1)	2
2114		28 (61.7)	2
4077	380 TO 480	28 (61.7)	2
4096		30 (66.1)	2
4124		33 (72.8)	2

□ denotes A-Z

1	CORRECTED MAIN TERMINAL HARDWARE
0	INITIAL RELEASE



UNITS MM [IN]
 SCALE 1:8

DRWN.	J. MATTAS	10-2-19
CHKD.	J. PIOTROWSKI	10-18-19
TECH.	L. UDDIN	10-21-19
APRV.	J. CAIRO	10-22-19



TITLE
 HV600 DIMENSION DRAWING
 FRAME SIZE 4
 IP55/UL TYPE 12 ENCLOSURE

SIZE	A	PAGE	1 OF 3
DWG.NO.		DD.HV60.FR4.T12	


REV 1

A B C D E F G H I J

1
2
3
4
5
6
7
8



EMC FILTER SWITCHES



C/C: HV60□	TERMINAL SYMBOL	WIRE RANGE AWG (mm ²)	TERMINAL SCREW	CLAMPING TORQUE N.m. (lb.in.)
2075□□□	R/L1, S/L2, T/L3	8 - 2/0 (10 - 70)	M8	6 (53)
2088□□□	U/T1, V/T2, W/T3	8 - 2/0 (10 - 70)	M8	6 (53)
2114□□□	- , +1	8 - 2/0 (10 - 70)	M8	6 (53)
4077□□□	⊕	8 - 2/0 (10 - 70)	M8	9 - 11 (79.7 - 97.4)
4096□□□				
4124□□□				

□ Denotes A-Z
Note: Refer to applicable codes and standards for proper wire type and size.

1	CORRECTED MAIN TERMINAL HARDWARE
0	INITIAL RELEASE




DRWN.	J. MATTAS	10-2-19
CHKD.	J. PIOTROWSKI	10-18-19
TECH.	L. UDDIN	10-21-19
APRV.	J. CAIRO	10-22-19

TITLE
HV600 DIMENSION DRAWING
FRAME SIZE 4
IP55/UL TYPE 12 ENCLOSURE

SIZE	A	PAGE	2 OF 3
DWG.NO.	DD.HV60.FR4.T12		

REV
1

Minimum Installation Clearances



Note:
For alternate mounting configurations, consult manual.

1	CORRECTED MAIN TERMINAL HARDWARE
0	INITIAL RELEASE



	UNITS MM [IN]
	SCALE 1:6

DRWN.	J. MATTAS	10-2-19
CHKD.	J. PIOTROWSKI	10-18-19
TECH.	L. UDDIN	10-21-19
APRV.	J. CAIRO	10-22-19

TITLE	HV600 DIMENSION DRAWING FRAME SIZE 4 IP55/UL TYPE 12 ENCLOSURE
-------	--

SIZE	A	PAGE	3 OF 3
DWG.NO.	DD.HV60.FR4.T12		

REV	1
-----	---