



(3)-M12 POWER TERMINALS
 MAX CLAMPING TORQUE: 177 +/- 17.7 lb.in.
 (20 +/- 2 N.m.)



NOTES:
 1. MOUNTING ORIENTATION MUST BE SUCH THAT POWER TERMINALS ARE FACING UP
 2. OUTER SIDES MAY BE BOWED AS SHOWN

ELECTRICAL DIAGRAM



FRONT VIEW

PART #	VOLTAGE (VAC)	CURRENT (Arms)	CAPACITANCE (uF +/-10%)	FREQUENCY (HZ)	WEIGHT LBS (Kg)	HEAT LOSS (W)
UCA000062	528	110	290	50/60	59 (27)	29

FOR ADDITIONAL DETAILS AND SPECIFICATIONS, CONSULT MANUAL

TOLERANCES / REFERENCES:			DRAWN: J. MATTAS DATE: 8-18-14	TITLE: DIMENSION DRAWING CAPACITOR UCA000062	
UNITS: IN [mm]	SCALE: 1:5		CHECKED: J. BORJA DATE: 9-17-14	SIZE A	REVISION R00
THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA, INC.		TECH: J. PIOTROWSKI DATE: 9-17-14	APPROVED: J. CAIRO DATE: 9-22-14	DRAWING #: DD.UCA000062	
		ORIGINAL DESIGN: -	DATE: -		