

| INPUT VOLTS | TERMINALS | | JUMPER LOCATION |
|-------------|-----------|------|------------------------------|
| | A | B | |
| 230/240 | (H1) | (H4) | (H1) TO (H3) (H2) TO (H4) |
| 460/480 | (H1) | (H4) | (H2) TO (H3) |
| 600 | (H1) | (H2) | NONE |

| BLOWER MOTOR | | |
|--------------|-----------|-------|
| FLA RATING | AMPS | VOLTS |
| 3.0 | 4.2 - 360 | 240 |
| 1.5 | 2.1 - 477 | 480 |
| 3.0 | 515 - 720 | 480 |

| CONTACT | POSITION | | | MANUF. LOCATION /TYPE |
|---------|----------|-----|------|-----------------------|
| | HAND | OFF | AUTO | |
| 1 | X | | | 1RO |
| 2 | | | X | 1LO |
| 3 | X | | | 2RO |

| CONTACT | POSITION | | | MANUF. LOCATION /TYPE |
|---------|----------|-----|------|-----------------------|
| | HAND | OFF | AUTO | |
| 1 | X | | | 1RO |
| 2 | | | X | 1LO |
| 3 | | | X | 2LO |

YASKAWA


THIS DOCUMENT AND INFORMATION CONTAINED HEREIN ARE CONFIDENTIAL AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA INC.

| | | |
|-----------------------------|--------------|-------------------------------------------------------------------------------------|
| DRAWN BY: K. PEOPLES | DATE: 8/3/18 | TITLE: SCHEMATIC DIAGRAM GA800 CONFIGURED TYPE 12 NORMAL DUTY RATING WITH OPTION PJ |
| CHECKED: N. LAWS | DATE: 8/3/18 | REVISION: 02 |
| APPROVED: K. FLEIRL | DATE: 8/3/18 | SIZE: D |
| ORIGINAL DESIGN: K. PEOPLES | DATE: 8/3/18 | REVISION: 02 |

REV. 02: ADDED OPTION TB AND FRAME 11 WIRING (ECD # 10925, DRAWN BY KAP, DATE 10/23/20)

REV. 01: CHANGED CN2-2 TO CN2 (ECD # 10780, DRAWN BY KG, DATE 8/19/20)

DRAWING # DS. G8C12.04



NOTES:

- CONNECTED TO THE CABINET. CUSTOMER TO CONNECT THE CABINET GROUND LUG TO EARTH GROUND.
- CONDUIT FITTINGS/HUBS SHALL COMPLY WITH THE 'STANDARD FOR CONDUIT, TUBING, AND CABLE FITTINGS, UL 514B', OR CONDUIT FITTINGS HAVING THE SAME ENVIRONMENTAL RATING AS THE ENCLOSURE SHALL BE USED.
- INSULATED TWISTED SHIELDED WIRE IS REQUIRED. SHIELD TO CONNECT TO PROPER TERMINALS AS SHOWN. CONNECT THE SHIELD ONLY AT THIS END. STUB AND ISOLATE THE OTHER END. DO NOT RUN THESE WIRES IN THE SAME CONDUIT AS THE AC POWER AND AC CONTROL WIRES. KEEP ALL WIRING UNDER 50m IN LENGTH.
- FOR A CONTROL TRANSFORMER T1 POWER RATING OF 350VA OR GREATER, SECONDARY FUSE F6 IS ADDED.
- CUSTOMER TO CONNECT NORMALLY OPEN BRAKING RESISTOR THERMAL SWITCHES PER THE GA800 TECHNICAL MANUAL IN PARALLEL WITH TB1-7 AND TB1-8.
- IF AC MOTOR IS FURNISHED WITH A N.C. THERMAL SWITCH THEN SET DRIVE PARAMETER H1-08 TO 27. THIS WILL CAUSE THE DRIVE TO COAST TO STOP UPON A AC MOTOR THERMAL FAULT. ALONG WITH THIS, ADD THE FOLLOWING CUSTOMER WIRING: WIRE THE N.C. THERMAL SWITCH BETWEEN DRIVE TERMINALS S8 AND SN, AS PER NOTE 3 ABOVE.
- OPTIONS TC, TD, TG, TH OR TQ CONTROL (SEE UDE00600 FOR MORE INFORMATION):
 OPTION TC = PROFINET
 OPTION TD = ETHERNET/IP
 OPTION TG = DEVICENET
 OPTION TH = PROFIBUS
 OPTION TQ = ETHERNET MODBUS TCP/IP
- DRIVE INPUT FUSES F3, F4, F5 ARE INCLUDED WITH OPTION PE, PC, PM, OR PJ FOR BASE NUMBERS B065-B720.
- DRIVE INPUT FUSES F3, F4, F5 ARE INCLUDED WITH OPTION TB FOR BASE NUMBERS A004-A009 AND B002-B007.

--- INDICATES CUSTOMER WIRING.
 --- CONNECTED TO THE CABINET OR PANEL.

FOR BASE NO'S
 A360, B361, B515-B720
 SEE GA800
 TECHNICAL MANUAL
 FOR WIRING
 INSTRUCTIONS

OPTION PJ
 DYNAMIC BRAKING
 WITH DB RESISTOR
 OVERTEMPERATURE
 SHUTDOWN

| | | | | |
|----------------|-------------------------------------|--------------------------------|-----------------|-------------------------------------------------------------------------------------------------|
| YASKAWA | | DRAWN BY: K. PEOPLES | DATE: 8/3/18 | TITLE: SCHEMATIC DIAGRAM GA800 CONFIGURED TYPE 12 NORMAL DUTY RATING WITH OPTION PJ |
| | | CHECKED: N. LAWS | DATE: 8/3/18 | |
| | | TECH: K. FLIERL | DATE: 8/3/18 | |
| | | APPROVED: K. PEOPLES | DATE: 8/3/18 | |
| | | ORIGINAL DESIGN: K. PEOPLES | DATE: 8/3/18 | |
| REV. | DESCRIPTION | ECD # | DRAWN BY | DATE |
| 02 | ADDED OPTION TB AND FRAME 11 WIRING | 10925 | KAP | 10/23/20 |
| 01 | CHANGED CN2-2 TO CN2 | 10780 | KG | 8/19/20 |
| | | | | SIZE: D |
| | | | | REVISION: 02 |
| | | | | PAGE: 2 of 2 |
| | | | | DRAWING #: DS.G8C12.04 |