



(6)-M12 POWER TERMINALS  
 MAX CLAMPING TORQUE:  
 177 +/- 17.7 lb.in.  
 (20 +/- 2 N.m.)



FRONT VIEW

NOTES:  
 1. MOUNTING ORIENTATION MUST BE SUCH THAT POWER TERMINALS ARE FACING UP  
 2. OUTER SIDES MAY BE BOWED AS SHOWN

ELECTRICAL DIAGRAM



PART #	VOLTAGE (VAC)	CURRENT (Arms)	CAPACITANCE (uF +/-10%)	FREQUENCY (HZ)	WEIGHT LBS (Kg)	HEAT LOSS (W)
UCA000064	528	307	800	50/60	121 (55)	111

FOR ADDITIONAL DETAILS AND SPECIFICATIONS, CONSULT MANUAL

TOLERANCES / REFERENCES:			DRAWN: <b>J. MATTAS</b> DATE: 8-18-14	TITLE: DIMENSION DRAWING CAPACITOR UCA000064
UNITS: IN [mm]	SCALE: 1:5		CHECKED: <b>J. BORJA</b> DATE: 9-17-14	TECH: <b>J. PIOTROWSKI</b> DATE: 9-17-14
THIS DOCUMENT AND INFORMATION CONTAINED IN IT ARE CONFIDENTIAL, AND CANNOT BE COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT THE EXPRESS WRITTEN CONSENT OF YASKAWA AMERICA, INC.		APPROVED: <b>J. CAIRO</b> DATE: 9-22-14	ORIGINAL DESIGN: -	SIZE: A REVISION: R00 PAGE: 1 of 1
			DRAWING #: <b>DD.UCA000064</b>	

SEE NOTE