


**DIMENSIONS: E7 (PROTECTED CHASSIS) 480V (414-675 AMPS)**

**S - 5519**



**S - 5519**

RATED INPUT	MODEL CIMR-E7U	RATED OUTPUT CURRENT (AMPS)	NOM. HP	DIMENSIONS IN INCHES									APPROX. WEIGHT (LBS.)
				MOUNTING		H	W	H2	W2	D	D1	A	
				H1	W1								
480V	41850	414	300-350	50.00	10.63	51.38	27.95	.79	3.35	16.34	4.94	3/8	572
	42200	515	400-450	50.00	10.63	51.38	27.95	.79	3.35	16.34	4.94	3/8	616
	43000	675	500	56.70	14.37	58.07	36.06	.79	3.66	16.34	4.94	3/8	891

FOR REFERENCE ONLY UNLESS PROPERLY ENDORSED.

IN ORDER TO ACHIEVE ADEQUATE COOLING  
THE DRIVE MUST BE POSITIONED TO ALLOW A MINIMUM  
OF FREE AIR OF 1.2 INCHES ON SIDES AND  
5 INCHES TOP AND BOTTOM