
### Super High Power Rate Series SGMS Servomotors (3000rpm) - With Incremental / Absolute

Encoder

Rated Output: 1.0kW, 1.5kW, 2.0kW, 3.0kW, 4.0kW, 5.0kW



For Additional Information	Page(s)
SGMS Ratings & Specifications	110
SGMS Speed/Torque Curves	111
SGMS Dimensions	112 - 115
SGMS Selection/Ordering Information	116 - 120
SGMS Optional CE Selection	121 - 125
SGDB Ratings & Specifications	129 - 130
SGDB Dimensions	131 - 137

#### **Design Features**

#### 1. Compact

- Small sized motor
  - Six frame sizes: up to 140 in. lb. RMS torque.

#### 2. High Speed

- Rated Speed: 3000 RPM
- Maximum Speed: 4500 RPM
- 3. Encoders
  - 4095 PPR incremental encoder standard
  - 8192 PPR absolute encoder (option)

#### 1. Enclosure

- Totally enclosed, self-cooled IP67 (excluding shaft)
- IP67 with shaft seal (option)

#### 5. Application Emphasis

- High torque to inertia ratio
- Chip mounters
- PCB drilling machines
- Robots
- Conveyors
- Packaging
- **ð. Certified International Standards** 
  - UL Recognized and c-UL pending (File # E165827), CE compliance (option)

# **Servomotor Ratings and Specifications**

Time Rating: Continuous Insulation: Class F Vibration: 15µm or less Withstand Voltage: 1500VAC Insulation Resistance: 500VDC  $10M\Omega$  min. Enclosure: Totally-enclosed, self-cooled Excitation: Permanent magnet IP67 (except for shaft opening) Drive Method: Direct drive Ambient Temperature: 0 to 40°C Ambient Humidity: 20 to 80% (non-condensing) Rated Speed: 3000 rpm Instantaneous Max Speed: 4500 rpm

Mounting: Flange-mounted Painting Color: Muncell notation N1.5

	Rated Output*		ted que*		eous Peak que*	Rated: Current*	Instantaneous Max. Current*
MOTORS: SGMS-	kW (HP)	N • M	kgf∙cm (lb∙in)	N • m	kgf • cm (lb • in)	A (ms)	A (ms)
10A□A	1.0 (1.3)	3.18	32.4 (28.2)	9.54	97.2 (84.4)	5.7	17
15A🗆A	1.5 (2.0)	4.9	50 (43)	14.7	150 (130)	9.5	28
20A□A	2.0 (2.7)	6.36	65 (56.4)	19.1	195 (169)	12.4	42
30A⊟A	3.0 (4.0)	9.8	100 (87)	29.4	300 (260)	18.8	56
40A□A	4.0 (5.4)	12.6	129 (112)	37.8	387 (336)	24.3	77
50A□A	5.0 (6.7)	15.8	161 (140)	47.6	486 (422)	28.2	84


NOTODO	Torque	e Constant	Moment	of Inertia	Hoiding Brake Torque	Holding Br	ake Inertia	Allowabie Load Inertia	Rated Power Rate*	Rated Angular Acceleration*	Time Time Constant	Inductive Time Constan
MOTORS: SGMS-	N • m/A (ms)	kgf•cm/A (ib•in/A) (rms)	kg <b>:</b> m <sup>2</sup> × 10 <sup>-4</sup>	gf•cm•s <sup>2</sup> (lb•in•s <sup>2</sup> × 10 <sup>-3</sup> )	N • m	kg • m² × 10 <sup>-4</sup> .	gf∙cm∙s <sup>2</sup> (lb∙in∙s <sup>2</sup> × 10 <sup>-3</sup> )	kg • m <sup>2</sup> × 10 <sup>-4</sup>	kW/s	rad/s <sup>2</sup>	ms	ms
10A⊟A	0.64	6.5 (5.6)	1.74	1.78 (1.54)				1.74	57.9	18250	0.87	7.1
15A⊟A	0.57	5.8 (5.1)	2.47	2.52 (2.19)	7.84	0.215	0.219 (0.190)	2.47	97.2	19840	0.71	7.7
20A□A	0.56	5.7 (5.0)	3.19	3.26 (2.82)	1			3.19	127	19970	0.58	8.3
30A🗆 A	0.57	5.8 (5.1)	7.00	7.14 (6.20)				7.0	137	14000	0.74	13.0
40A□A	0.55	5.6 (4.9)	9.60	9.80 (8.50)	2.0	1.85	1.89 (1.64)	9.6	166	13160	0.60	14.1
50A🗆 A	0.61	6.2 (5.4)	12.3	12.6 (10.9)			(	12.3	202	12780	0.57	14.7

\* These items and torque-speed characteristics quoted in combination with an SGDB Servo Amplifier at an armature winding temperature of 20°C.

Note: These characteristics can be obtained when the following heat sinks (steel plates) are used for cooling purposes:

Type 10A□A to 20A□A: 300 × 300 × 12 (mm)	(11.81 × 11.81 × 0.47 (in))
Type 30A□A to 50A□A: 400 × 400 × 20 (mm)	(15.75 × 15.75 × 0.79 (in))


# **Speed / Torque Curves**



SMDS

# **Dimensions in inches (mm)**

(1) 4096 PPR Incremental Encoder



Type SGMS-	۲. ۲	ĽĽ,	LM	LR	LT	KB1	KB2	KL1	KL2			Flan	ge Dim	ensions				Shaft E Dimens		Approx. Mass
30m3-8	å. 	2 ES		12010			22222			LA	LB	. LC -	LE	LG	,LH∵	LJ	LZ	S	/ Q ×	<b>i</b> b (kg)
10A6AB	7.64 (194)	5.87 (149)	4.06 (103)	1.77 (45)	1.81 (46)	2.99 (76)	5.04 (128)	3.78 (96)	3.43 (87)	4.53 (115)	3.74 (95) \$ <sub>035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) -8013	1.57 (40)	10.1 (4.6)
15A6AB	8.66 (220)	6.89 (175)	5.08 (129)	1.77 (45)	1.81 (46)	4.02 (102)	6.06 (154)	3.78 (96)	3.43 (87)	4.53 (115)	3.74 (95) 8 <sub>.035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) -0 013	1.57 (40)	12.8 (5.8)
20A6AB	9.57 (243)	7.8 (198)	5.98 (152)	1.77 (45)	1.81 (46)	4.92 (125)	6.97 (177)	3.78 (96)	3.43 (87)	4.53 (115)	3.74 (95) 8 <sub>035</sub>	3.94 (100)	0.12 (3)	0.3 <del>9</del> (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) -0 013	1.57 (40)	15.4 (7.0)
3046AB	10.31 (262)	7.83 (199)	6.02 (153)	2.48 (63)	1.81 (46)	4.8 (122)	7.01 (178)	4.49 (114)	3.43 (87)	5.71 (145)	4.33 (110) _8. <sub>035</sub>	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	1.1 (28) -8013	2.17 (55)	24.3 (11)
40A6AB	11.77 (299)	9.29 (236)	7.48 (190)	2.48 (63)	1.81 (46)	6.26 (159)	8.46 (215)	4.49 (114)	3.43 (87)	5.71 (145)	110 (4.33) -0.0014	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1.77 ( <b>45</b> )	0.25 (0)	11	2.17 (55)	30.9 (14)
50A6AB	13.35 (339)	10.87 (276)	9.06 (230)	2.48 (63)	1.81 (46)	7.83 (199)	10.04 (255)	4.49 (114)	3.43 (87)	5.71	110 (4.33) -8 0014	5.12 ( <b>130</b> )	0.24 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	11	2.17 (55)	37.5 (17)

1. Incremental Encoder (4096 PPR) is used as a detector.

2. Dimensions are the same when using other incremental encoders.

3. Tolerances on the dimensions LB of flange type and S of shaft extensions are based on JIS (Japanese Industrial Standard) B0401 "Limits and Fits for Engineering." 4. There are no dimensional changes on the CE products.

**Connector Specifications** 

Receptacle: MS3102A20-29P Applicable Plug: (To be prepared by customer) Plug: MS3108B20-29S (L Type) MS3106B20-29S (Straight Type) Cable Clamp: MS3057-12A






	Connector Wiring on the	Increa	nental Encoder
Α	Channel A Output	к	
в	Channel A Output	L	
с	Channel B Output	M	-
D	Channel B Output	N	-
E	Channel C Output	Р	•
۶	Channel C Output	R	-
G	0V	S	-
Н	+5 VDC	Т	-
J	FG (Frame Ground)		

Con	nector Wiring on the Motor Side
A	U Phase
В	V Phase
C	W Phase
D	Ground Terminal

Note: The above-mentioned detector side specifications are common to all the motors with incremental encoders.

### (2) 4096 PPR Incremental Encoder, with Brake



Type SGMS-	L	LL ,	LM	-LR	LT	: - <b>KB</b> 1	KB2	KL1	КІ.2		راد بر می ماند بر	Flar	ige Dim	ensions	`ai T	s i la c	dan da	Shaft E Dimens		Approx. Mass
· · ·	1 A.	****								LA	LB	- LC	LE	ĽG	LH	IJ	ίΖ	S	Q: .	ib (kg)
10A6ABC	9.37 (238)	7.6 (193)	5.79 (147)	1.77 (45)	1.81 (46)	2.64 (67)	6.77 (172)	3.94 (100)	3.43 (87)	4.53 (115)	3.74 (95) -8.035	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) _8 <sub>.013</sub>	1.57 (40)	13.2 (6.0)
15A6ABC	10.39 (264)	8.62 (219)	6.81 (173)	1.77 (45)	1.81 (46)	3.66 (93)	7.8 (198)	3.94 (100)	3.43 (87)	4.53 (115)	3.74 (95) _8 <sub>.035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) <sub>-0 013</sub>	1.57 (40)	16.5 (7.5)
20A6ABC	11.3 (287)	9.53 (242)	7.72 (196)	1.77 (45)	1.81 (46)	4.57 (116)	8.7 (221)	3.94 (100)	3.43 (87)	4.53 (115)	3.74 (95) -8.035	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) -8 <sub>.013</sub>	1.57 (40)	18.7 (8.5)
30A6ABC	11.81 (300)	9.33 (237)	7.52 (191)	2.48 (63)	1.81 (46)	4.45 (113)	8.5 (216)	4.69 (119)	3.43 (87)	5.71 (145)	4.33 (110) -8.035	5.12 (130)	0 <i>2</i> 4 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	1.1 (28) _0 <sub>013</sub>	2.17 (55)	30.9 (14)
40A6ABC	13.27 (337)	10.79 (274)	8.96 (228)	2.48 (63)	1.81 (46)	5.91 (150)	9.96 (253)	4.69 (119)	3.43 (87)	5.71 (145)	4.33 (110) -8.035	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	1.1 (28) _8 <sub>013</sub>	2.17 (55)	37.5 (17)
50A6ABC	13.27 (377)	12.36 (314)	10.55 (268)	2.48 (63)	1.81 (46)	7.48 (190)	11.54 (293)	4.69 (119)	3.43 (87)	5.71 (145)	4.33 (110) -8 035	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	1.1 (28) -8 <sub>013</sub>	2.17 (55)	44.1 (20)

Note: 1. Incremental Encoder (4096 PPR) is used as a detector.

Dimensions are the same when using other incremental encoders.
 Dierances on the dimensions 18 of flange type and S of shaft extensions are based on JIS (Japanese Industrial Standard) B0401 "Limits and Fits for a second se


Engineering."

4. There are no dimensional changes on the CE products.



,	Connector Wiring on the Motor Side								
A	U Phase	E	Brake Terminal						
В	V Phase	F	Brake Terminal						
С	W Phase	G	-						
D	FG Frame Ground								

### (3) 8192 PPR Absolute Encoder (15 bit)



Type SGMS-		Ú.	LM	LR	LT:	KB1	KB2	KL1	KL2			Flar	ige Dim	ensions				Shaft E Dimens		Approx. Mass
0000		*. *		·			101.07			±LA -	LB	. LC	LE	ŁG	LH	IJ	LZ	S	· Q ·	lb (kg)
10ASAB	8.19 (208)	6.42 (163)	4.06 (103)	1.77 (45)	2.36 (60)	2.9 <del>9</del> (76)	5.59 (142)	3.78 (96)	3.43 (87)	4.53 (115)	3.74 (95) 3 <sub>035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 ( <b>130</b> )	1.77 (45)	0.28(7)	0.94 (24) 8 <sub>.013</sub>	1.57 (40)	11 (5.0)
15ASAB	9.21 (234)	7.44 (189)	5.08 (129)	1.77 (45)	2.36 (60)	4.02 (102)	6.61 (168)	3.78 (96)	3.43 (87)	4.53 (115)	3.74 (95) -8 <sub>.035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) <sup>0</sup> 013	1.57 (40)	13.7 (6.2)
20ASAB	10.12 (257)	8.35 (212)	5.98 (152)	1.77 (45)	2.36 (60)	4.92 (125)	7.52 (191)	3.78 (96)	3.43 (87)	4.53 (115)	3.74 (95) 2035	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) -8 <sub>013</sub>	1.57 (40)	16.3 (7.4)
30ASAB	10.87 (276)	8.39 (213)	6.02 (153)	2.48 (63)	2.36 (60)	4.8 (122)	7.56 (192)	4.49 (114)	3.43 (87)	5.71 (145)	4.33 (110) 2 <sub>035</sub>	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	11	2.17 (55)	25.4 (11.5)
40ASAB	12.32 (313)	9.84 (250)	7.48 (190)	2.48 (63)	2.36 (60)	6.26 (159)	9.02 (229)	4.49 (114)	3.43 (87)	5.71 (145)	4.33 (110) <u>}.035</u>	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1.77 (45)	0.35 (9)	11	2.17 (55)	32 (14.5)
50ASAB	13.9 (353)	11.42 (290)	9.06 (230)	2.48 (63)	2.36 (60)	7.83 (199)	10.59 (269)	4.49 (114)	3.43 (87)	5.71 (145)	4.33 (110) _8 <sub>.035</sub>	5.12 (130)	0.24 (6)	0.47 (12)	6.5 (165)	1,77 (45)	0.35 (9)	11	2.17 (55)	38.6 (17.5)
Note:	. Incre	mental	Encode	r (81926	6 PPR)	is used	as a de	tector.												


1. Incremental Encoder (81926 PPR) is used as a detector.

2. Dimensions are the same when using other incremental encoders.

3. Tolerances on the dimensions LB of flange type and S of shaft extensions are based on JIS (Japanese Industrial Standard) B0401 "Limits and Fits for Engineering."

4. There are no dimensional changes on the CE products.

**Connector Specifications** Receptacle: MS3102A20-29P Applicable Plug: (To be prepared by customer) Plug: MS3108B20-29S (L Type) MS3106B20-29S (Straight Type) Cable Clamp: MS3057-12A




	Connector Wiring on the (When using 8192		
Α	Channel A Output	к	-
В	Channel A Output	L	-
С	Channel B Output	м	-
D	Channel B Output	N	-
E	Channel Z (C) Output	Ρ	-
F	Channel Z (C) Output	R	Reset
G	0V	S	0V (battery)
Н	+5 VDC	T	3.6V (battery)
J	FG (Frame Ground)		
Note:	The above-mentioned de	tector :	side specifications are

common to all the motors with incremental encoders.

Conn	ector Wiring on the Motor Side
A	U Phase
В	V Phase
С	W Phase
Ď	FG (Frame Ground)



### (4) 8192 PPR Absolute Encoder (15 bit), With Brake



Type	- <b>- 1</b>	с КЦСТ	LM	١R	LT	KB1	KB2	KL1	KL2			Flar	ige Dim	ensions	1. 39 1. 1. 1			Shaft E		Approx. Mass
SGMS		11 Sep 11	3	$C \oplus$	*****	51-14 - 17 1		· ,		LA	LB	LC		∙;LG ∝	» LH	i LJ	i LZ	S	Q	b (kg)
10ASABC	9.92 (252)	8.15 (207)	5.79 (147)	1.77 (45)	2.36 (60)	2.64 (67)	7.32 (186)	3.94 (100)	3.43 (87)	4.53 (115)	3.74 (95) .8 <sub>035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) 8 <sub>.013</sub>	1.57 (40)	14.3 (65)
15ASABC	10.94 (278)	9.17 (233)	6.81 (173)	1.77 (45)	2.36 (60)	3.66 (93)	8.35 (212)	3.94 (100)	3.43 (87)	4.53 (115)	3.74 (95) 3 <sub>035</sub>	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28(7)	0.94 (24) 8 <sub>013</sub>	1.57 (40)	17.6 (8.0)
20ASABC	11.85 (301)	10.08 (256)	7.72 (196)	1.77 (45)	2.36 (60)	4.57 (116)	9.25 (235)	3.94 (100)	3.43 (87)	4.53 (115)	3.74 (95) 0.035	3.94 (100)	0.12 (3)	0.39 (10)	5.12 (130)	1.77 (45)	0.28 (7)	0.94 (24) <sup>0</sup> 013	1,57 (40)	19.8 (9.0)
30ASABC	12.36 (314)	9.88 (251)	7.52 (191)	2.48 (63)	2.36 (60)	4.45 (113)	9.06 (230)	4.69 (119)	3.43 (87)	5.71 (145)	4.33 (110) _8 <sub>035</sub>	5.12 (130)	0.24 (6)	0.47 (2)	6.5 (165)	1.77 (45)	0.35 (9)	1.1 (28) <u>8 <sub>013</sub></u>	2.17 (55)	32 (14.5)
40ASABC	13.82 (351)	11.34 (288)	8.98 (228)	2.48 (63)	2.36 (60)	5.91 (150)	10.51 (267)	4.6 <del>9</del> (119)	3.43 (87)	5.71 (1 <b>45</b> )	4.33 (110) <u>8.035</u>	5.12 (130)	0.24 (6)	0.47 (2)	6.5 (165)	1.77 (45)	0.35 (9)	1.1 (28) 8 <sub>013</sub>	2.17 (55)	38.6 (17.5)
50ASABC	15.39 (391)	12.91 (328)	10.55 (268)	2.48 (63)	2.36 (60)	7,48 (190)	12.09 (307)	4.69 (119)	3.43 (87)	5.71 (145)	4.33 (110) 8.035	5.12 (130)	0.24 (6)	0.47 (2)	6.5 (165)	1,77 (45)	0.35 (9)	1.1 (28)	2.17 (55)	45.2 (20.5)

 Dimensions are the same when using other incremental encoders.
 Tolerances on the dimensions LB of flange type and S of shaft extensions are based on JIS (Japanese Industrial Standard) B0401 "Limits and Fits for Engineering."

4. There are no dimensional changes on the C€ products.





Connector Wiring on the Motor Side 2								
A	U Phase	E	Brake Terminal					
В	V Phase	F	Brake Terminal					
С	W Phase	G	-					
D	FG (Frame Ground)							

# **Selecting Your SGMS Sigma Servo System**

Use the diagram below to locate and identify the components of your system. Each item is letter-coded and cross-referenced in the option tables on the following pages.

### System Configuration





Note: **Bold** items are Stock Products usually available from inventory. Contact your Yaskawa representative for delivery on all other items.

# Servomotor & Amplifier Selection

#### Use the table below to select the appropriate SGMS Sigma Servomotor and Amplifier.

Description	Peak Torque (in. lb.)	Rated Torque (in. lb.)	Motor Inertia (in. lb. sec <sup>2</sup> x 10 <sup>-3</sup> )	Motor MODEL # (A)	Amplifier MODEL # <b>(B)*</b> Analog/Digital Input SGDB-	Motor & Amplifier Item Class	
	04.4	20.0	4 5 4	SGMS-10A6AB	10ADG		
	84. <b>4</b>	28.2	1.54	SGMS-10A6ABC	IUADO	- Stock	
200V	400	40	0.40	SGMS-15A6AB	15ADG		
3-Phase	130	43	2.19	SGMS-15A6ABC	IJADG		
4096 PPR	400	50.4	2.92	SGMS-20A6AB	20ADG		
Incremental Encoder	169	56.4	2.82	SGMS-20A6ABC	20400		
Straight Shaft	200	07	6.2	SGMS-30A6AB	30ADG		
with	260	87	0.2	SGMS-30A6ABC	30700		
Keyway		110	0.5	SGMS-40A6AB			
MS Connectors	336	112	8.5	SGMS-40A6ABC	44ADG		
	400	140	11	SGMS-50A6AB	447.00		
	422	140	11	SGMS-50A6ABC	]		

Note: 24VDC brakes for SGMS Sigma servomotors are standard. Contact a local source for 24VDC power supplies. For technical information, request manual number TSE-S800-16 from your Yaskawa representative.

\* For more detailed SGDB amplifier specifications and dimensions, refer to page 127.

### Pre-wired Cable Selection

#### Use the table below to select Pre-wired Cables for your SGMS Sigma Servomotor.

				lumber			
Cable Des	scription <b>(C)</b>	Size (kW)	without Brake	with Brake	Comments	Item Class	
Power Cable with		1.0, 1.5, 2.0	B1E-□	B1BE-D			
L-type Connectors		3.0	B2E-□	B2BE-	Use the following key to specify required cable length		
		4.0, 5.0	B3E-□	B3BE-□	(last digit of part #): 1: 3 meters		
Encoder Cable (incremental or absolute)			DE9407237-□E		<ol> <li>2: 5 meters</li> <li>3: 10 meters (standard)</li> <li>4: 15 meters</li> <li>5: 20 meters</li> </ol>		
Encoder Cable Only for Solder Connections			DP8409123		Up to 70 feet; for use with mating connector.		
Encoder Cable Only for Solder Connections		All	DP84(	09179	Over 70 feet; splice cable to accommodate connector.	Stock *	
Input/Output 1CN Cable & Transition Terminal Block		7"	JUSP-	TA50P	35 mm din rail mountable; the cable length is 0.5 meters.		
Input/Output 1CN Cable with Pigtail Leads			DE9406969-ロ		Use the following key to specify required cable length (last digit of part #): 1: 1 meter (standard) 2: 2 meters 3: 3 meters		

\* Standard cable lengths are Stock items; non-standard cable lengths are Limited Stock items.

# Mating Connector Selection

#### Use the table below to select Mating Connectors for your SGMS Sigma Servomotor.

Connector Des	cription (D)	Motor Size (kW)	Part N without Brake	umber with Brake	Comments	Item Class
MS Connector		1.0, 1.5, 2.0	MS3106B18-10S MS3108B18-10S MS3057-10A	MS3106B20-15S MS3108B20-15S MS3057-12A	Straight-type connector L-type connector Cable clamp	
for Motor Power Cable *		3.0, 4.0, 5.0	MS3106B22-22S MS3108B22-22S MS3057-12A	MS3106B24-10S MS3108B24-10S MS3057-16A	Straight-type connector L-type connector Cable clamp	
MS Connector for Encoder Cable (incremental or absolute encoder)			MS3108	B20-29S B20-29S 57-12A	Straight-type connector L-type connector Cable clamp	Stock
1CN Mating Connector			DE94	06970	Can use 1CN for ana- log speed and torque monitor service checks.	
2CN Encoder Mating Connector		All	DE9406973		_	
3CN Peripheral Mating Connector			Stock 9-pin male	D-shell connector	Source locally.	-
5CN Connector and 1m Cable with Pigtails			DE94	404559	_	Stock

\* Choose either a straight or L-type connector and the associated cable clamp for a complete assembly. For example, L-type connector MS3108B18-10S is compatible with cable clamp MS3057-10A.

# Peripheral Device Selection


#### Use the table below to select Peripheral Devices for your SGMS Sigma Servomotor.


Compo	nent (E)	Part Number	Description	Item Class
Hand-held Digital Operator Panel		JUSP-OP02A-1	Portable unit with built-in cable	Stock
Digital Operator Panel	SERVOPACK	JUSP-OP03A	Plugs into front of amplifier	Non-Stock
SVMON Software		SVMON	Programming software for DOS 3.3 on a 3.5" floppy disk	Stock
Software Interface Cable		YS-11	Pre-wired 1.5 meter cable with 9-pin connector	

# Selecting Your SGMS Sigma Servo System

Use the diagram below to locate and identify the components of your system. Each item is letter-coded and cross-referenced in the option tables on the following pages.

### System Configuration





S: 8192PPR Absolute Encoder

#### **Optional CE**

### Servomotor & Amplifier Selection

#### Use the table below to select the appropriate SGMS Sigma Servomotor and Amplifier.

Description	• Peak Torque (in. lb.)	Rated Torque (in.lb)	Motor Inertia (in. lb sec <sup>2</sup> × 10 <sup>-3</sup> )	Motor MODEL # (A)	Amplifier MODEL # <b>(B)*</b> Analog/Digital Input SGDB-	Motor Item Class
	84.4	28.2	1.54	SGMS-10V6AB	10VD (Limited Stock)	Limited Stock
				SGMS-10V6ABB	(Limited Stock)	Non-Stock
	130	43	2.19	SGMS-15V6AB	15VD (Limited Stock)	Limited Stock
200V 3-Phase				SGMS-15V6ABB	(Limited Stock)	Non-Stock
4096 PPR	169	56.4	2.82	SGMS-20V6AB	20VD (Limited Stock)	Limited Stock
Incremental Encoder				SGMS-20V6ABB	(Linited Stock)	Non-Stock
Straight Shaft with	260	87	6.2	SGMS-30V6AB	30VD (Limited Stock)	Limited Stock
Keyway				SGMS-30V6ABB	(Limited Stock)	Non-Stock
MS Connectors	336	112	8.5	SGMS-40V6AB	60VDY6	Limited Stock
				SGMS-40V6ABB	(Limited Stock)	Non-Stock
	422	422 140		SGMS-50V6AB	60VDY7	Limited Stock
				SGMS-50V6ABB	(Limited Stock)	Non-Stock



Note: 90VDC brakes for SGMS Sigma servomotors (CE) are standard. See Peripheral Device Selection in this section to order a power supply.

For technical information, request technical document numbers PI-6021 and DE9409784 from your Yaskawa representative.

\* For more detailed SGDB amplifier specifications and dimensions, refer to page 127.

#### Optional CE

### SGMS Sigma Servo System

### Pre-wired Cable Selection

#### Use the table below to select Pre-wired Cables for your SGMS Sigma Servomotor.

		Motor	Part N	Number			
Cable Desc	cription (C)	Size (kW)	without Brake	with Brake	Comments	Item Class	
Power Cable with		1.0, 1.5, 2.0	B1CE-□	B1BCE-□	Use the following key to spec-	Limited	
Connectors		3.0	B2CE-	B2BCE-	ify required cable length (last digit of part #):	Stock	
		4.0, 5.0	B3CE-□	B3BCE-	1. 3 meters 2: 5 meters		
Encoder Cable (incremental or absolute)			A1CE-D		<ul><li>3: 10 meters (standard)</li><li>4: 15 meters</li><li>5: 20 meters</li></ul>	Limited Stock	
Encoder Cable Only for Solder Connections			DP84	09123	Up to 70 feet; for use with mating connector.		
Encoder Cable Only for Solder Connections	- <u> </u>		DP84	409179	Over 70 feet; splice cable to accommodate connector.		
Input/Output 1CN Cable & Transition Terminal Block		All		-TA50P	35 mm din rail mountable; the cable length is 0.5 meters.	Stock *	
Input/Output 1CN Cable with Pigtail Leads			DE940	)6969-□	Use the following key to specify required cable length (last digit of part #): 1: 1 meter (standard) 2: 2 meters 3: 3 meters		

\* Standard cable lengths are Stock items; non-standard cable lengths are Limited Stock items.

#### **Optional CE**

# Mating Connector Selection

#### Use the table below to select Mating Connectors for your SGMS Sigma Servomotor.

Connector Description (D)		Motor Size	Part N	Comments	Item	
Connector De	escription (U)	(kW)	without Brake	with Brake	Comments	Class
	••••••••••••••••••••••••••••••••••••••	1.0, 1.5,		JL04V-8A20-15SE-EB	L-type	
Connector for		2.0	JL04-18CK(13)	JL04-2022CK(14)	connector Cable clamp	
Motor Power Cable *		3.0, 4.0,	JL04V-8A22-22SE-EB	JL04V-8A24-10SE-EB	L-type connector	
		5.0	JL04-2022CK(14)	JL04-2428CK(17)	Cable clamp	J
Connector for Encoder Cable (incremental or absolute encoder)			JA08A-20- JL04-202	L-type connector Cable clamp	Limited Stock	
1CN Mating Connector		1	DE94	Can use 1CN for analog speed and torque monitor service checks.		
2CN Encoder Mating Connector		All	DE94	-		
3CN Periph- eral Mating Connector			Stock 9-pin male	Source locally.	_	
5CN Connec- tor and 1m Cable with Pigtails			DE940	-	Limited Stock	

\* Choose the connector and the associated cable clamp for a complete assembly.

SUNDS

#### **Optional CE**

# SGMS Sigma Servo System

# **Peripheral Device Selection**

Use the table below to select Peripheral Devices for your SGMS Sigma Servomotor.

Compoi	nent ( <b>E</b> )	Part Number	Description	Item Class
Hand-held Digital Operator Panel		JUSP-OP02A-1	Portable unit with built-in cable	Stock
Digital Operator Panel	SERVOPACK	JUSP-OP03A	Plugs into front of amplifier	Non-Stock
SVMON Software		SVMON	Programming software for DOS 3.3 on a 3.5" floppy disk	Stock
Software Interface Cable		YS-11	Pre-wired 1.5 meter cable with 9-pin connector	

### NOTES

