

14	15	16	17
		1L1	
•		to 202	A
		1L2	
		to 203	
-{{			
L1 L2 L3	I		
			В
K8 OV	•		
VOLTAGE VOLT MONITOR PROTE			
RELAY			
	İ		
21 22	Ì		
121	Ì		с
120 121	I		
to 224 to 224	I		
			D
NOTES:			
	TED TO THE CABINE <sup>-</sup> T THE CABINET GRO		
EARTH G	ROUND AND UTILITY	GROUND.	
	ED TWISTED SHIELD		
TERMINA	L AS SHOWN. CONN	ECT THE SHIELD	E
	THIS END. STUB AND ND. DO NOT RUN TH		
SAME CC	NDUIT AS THE AC PO	OWER AND THE AC	
CONTRO IN LENGT	L WIRES. KEEP ALL ' 'H.	WIRING UNDER 50m	
3. WITH A C	ONTROL TRANSFOR		
RATING 3 F6 IS ADD	350VA OR GREATER, DED.	SECONDARY FUSE	
4. WITHOUT	THE INPUT CIRCUIT		F
	HEN NOTED ON THE TE, BRANCH CIRCU		
MUST TH	E SUPPLIED BY THE	INSTALLER.	
	ER TO ADJUST THE 1 CE HEATER HR1 FOR		
DESIRED	TEMPERATURE INS	IDE THE DRIVE	
	. THIS SET TEMPERA D TO BE SLIGHTLY F		
MINIMUM	AMBIENT TEMPERA	TURE OF THE AIR	G
	NDING THE CABINET ATURE AT WHICH THI		
HR1 WILI	_ SHUT OFF.		
	FITTINGS/HUBS SHA		
CABLE FI	TTINGS, UL 514B' OR	CONDUIT FITTINGS	
	THE SAME ENVIRON LOSURE SHALL BE U		
7. TERMINA	LS p1 AND n1 ARE F	OR MOMENTARY	
	OSS RECOVERY UN T TO AC POWER SUP		н
8. CUSTOM	ER TO REPLACE THE	JUMPER WITH	
NORMALI	LY CLOSED SAFETY BLE.	INTERLOCKS, IF	
- INDICATES (	JOINPONENTS NOT S	UPPLIED BY YASKAWA	
₭ - INDICATES (	CUSTOMER WIRING		L
- CONNECTER	TO THE CABINET O	R PANEL	
	G UDE00538 FOR DRI G UDE00539 FOR CU	VE PARAMETERS. STOMER CONNECTIONS.	
		,	
	DRAWN BY:	DATE TITLE:	
SKAWA	R. ROH CHECKED:	10/30/17 SCHEMATIC DIAGRA DATE U1000 IQPUMP COM	IFIGURED
	N. LAWS	12/01/17 TYPE 3R, 480V	K
ENT AND INFORMATION CONTAINL ONFIDENTIAL, AND CANNOT L	BF	SIZE RE	VISION PAGE
DISCLOSED IN WHOLE OR IN PA	K. FLIERL	12/01/17 DRAWING #:	03 1 of 2
HE EXPRESS WRITTEN CONSEI 'A AMERICA INC.	R. ROH	10/30/17 DS.Q1E3	.13
14	15	16	17

